


The production, distribution and utilization of this document is, as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All design and technical data is subject to change without notice. Weldon shanks produced with transition radius.

Bezeichnung **HM - Kugelfräser** Dok.-art **Dokumentationszeichnung**

Schneiden-Ø **1** Schneidenlänge **1** Gesamtlänge **60** Schaft-Ø **4**




Typ	N
Zähnezahl	2
Schneidrichtung	rechts
Spiralrichtung	Rechtsspirale
Spiralwinkel	30°
Teilung	gleich geteilt
Kühlung	ohne
Schaft	DIN 6535-HA
Beschichtung	TIALN
Bemerkung:	

Wichtig: Alle Rechte vorbehalten. Nachdruck, Vervielfältigung und Verbreitung, auch auszugsweise, ist ohne schriftliche Genehmigung der EMUGE-FRANKEN AG. Alle Rechte für den Fall der Patent-, Marken- und Schutzrechtsverletzung vorbehalten. Alle Maßangaben sind in mm anzunehmen, wenn nicht anders angegeben.



Blatt SHEET
 Masst. SCALE
 5:2



Allgemeintoleranzen ISO 2768-mk
 GENERAL TOLERANCES

>	6	30	120	400	1000
≤ 6	30	120	400	1000	2000
	±0,1	±0,2	±0,3	±0,5	±1,2

Dok.-art DOC. TYPE **Dokumentationszeichnung**
 Bezeichnung TITLE
FRANKEN - HM Kugelfräser

Ersteller Issued by **TA**
 Erstelldatum DATE **19-05-2016**

Ersetzt durch REPL. BY
 Ersatz für REPL. FOR

Kundencode CUSTOMER CODE
 Kunden-Sach-Nr. CUSTOMER PART NO.

Artikel-Nr. ARTICLE-NO.
 Zeichnungs-Nr. DRAWING-NO.

2774A.001