


The production, distribution and utilization of this document is, as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All design data is subject to change without notice. Weldon shanks produced with transition radius.

Bezeichnung **HM - Kugelfräser** Dok.-art **Dokumentationszeichnung**

Schneiden-Ø **1** Schneidlänge **0,6** Gesamtlänge **43** Schaft-Ø **4**



Typ	N
Zähnezahl	2
Schneidrichtung	rechts
Spiralrichtung	Rechtsspirale
Spiralwinkel	30°
Teilung	gleich geteilt
Kühlung	ohne
Schaft	DIN 6535-HA
Beschichtung	TIALN
Bemerkung:	

Wird eingeleitet sowie Vervielfältigung dieses Dokuments, Verwertung, Verbreitung, auch auszugsweise, ist ohne schriftliche Genehmigung der EMUGE FRANKEN AG. Die Rechte für den Fall der Patent-, Marken- und Schutzrechtsverletzung nach ISO 9016 behält sich EMUGE FRANKEN AG vorbehalten. Alle Maßangaben sind mit Übermaßangaben.



Blatt SHEET  
 Masst. SCALE  
 7:2

Ansicht VIEW  
 Projektionsmethode 1  
 FIRST ANGLE Projektion

Allgemeintoleranzen ISO 2768-mk  
 GENERAL TOLERANCES

>	6	30	120	400	1000
≤ 6	30	120	400	1000	2000
	±0,1	±0,2	±0,3	±0,5	±1,2

Dok.-art DOC. TYPE **Dokumentationszeichnung**  
 Bezeichnung TITLE  
**FRANKEN - HM Kugelfräser**

Ersteller Issued by **TA**

Erstelldatum DATE **19-05-2016**

Ersetzt durch REPL. BY

Kundencode CUSTOMER CODE

Artikel-Nr. ARTICLE-NO.

Prüfer Verified by

Prüfdatum DATE

Ersatz für REPL. FOR

Kunden-Sach-Nr. CUSTOMER PART NO.

Zeichnungs-Nr. DRAWING-NO. **2770A.001**